Fyreye MkII Addressable Input/ Output Module With Isolator (ZAIO-MI)






Features

- Loop powered (60 devices per loop as maximum)
- Mand addressed using the 8 way dip switch OR
- Softly addressed using our handheld MKII Programmer (part no. 48-004)
- Equipped with short circuit line isolator
- Extensive front unit indications

Typical Wiring Diagram



Front Unit Indications

FIGHT OTHER HIGHEST		
Status	LED Indication	
Switch closed	Illuminated red when monitored field contact is activated	
Relay on	Illuminated red when relay is energized	
Fault	Illuminated yellow when the input is open or short circuit	
Polling	Flashed green when the device is polled by control panel	
Isolating	Illuminated yellow when the loop is short or wrong connection circuit	

Description

The ZAIO-MI is both an input and output module in a modern enclosure (2 gang box size) with well protected electronic circuit board to minimize any damages during installation.


It is supplied with a back box suitable for surface mount indoor installation. Designed and manufactured to meet the requirements of EN54-18 2005 and EN54-17 2005.

The ZAIO-MI is used when both an input needs to be monitored and at the same time a local output (relay output) needs to be triggered to switch ancilliary equipment on or off during an alarm condition.

Typical output triggering includes: controlling lift operation during an alarm, starting fire pump, stopping ventilation fans etc.

For more details and connection information consult the installation guide.

Dimensions (mm) & Weight (g)



Technical Specification

rechnical Specification		
Model	ZAIO-MI	
Part Number	48-108	
Operating Voltage	17-28V DC	
Quiescent Current @ 24V	1.0mA	
Switch Input Closed (LED OFF)	1.25mA	
Relay Operated (LED ON)	2.0mA (Max 2 LEDs on)	
Relay Rating	SELV @ 1A	
Isolating Current	7.3mA	
Input End Of Line	20k	
Alarm Triggering Resistor	1k	
Operating Temperature	-10°C to +55°C	
Max Humidity	95% RH Non Condensing	
IP rating	IP21C	
Size (mm)	150 x 90 x 45	
Weight	220g	

Doc: GLT-233-6-1 Issue: 003 Date: 08/02/16